

# Clevis foot CRLNG-50

Part number: 161842

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	50
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	Any
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 80 °C
Max. load capacity	2.5 kN
Product weight	281 g
Note on materials	RoHS-compliant
Mounting material	Electropolished High-alloy steel
Material of bearing	Polymer