

Pivot pin CRZNG-50

Part number: 161854

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	50
Based on norm	ISO 15552
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	2.5 kN
Product weight	473 g
Note on materials	RoHS compliant
Mounting material	high-alloy stainless steel
Material of screws	high-alloy stainless steel