

# Pivot pin CRZNG-100

Part number: 161857

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value  |
|--|--|
| Size   | 100  |
| Based on norm                                      | ISO 15552  |
| Corrosion resistance class (CRC)                   | 4 - Particularly high corrosion stress   |
| LABS (PWIS) conformity                             | VDMA24364-B2-L   |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Ambient temperature                                | -40 °C ... 150 °C  |
| Max. load capacity                                 | 9 kN   |
| Product weight                                     | 2254 g   |
| Note on materials                                  | RoHS compliant   |
| Mounting material                                  | high-alloy stainless steel   |
| Material of screws                                 | high-alloy stainless steel   |