

Fine filter combination LFMBA-1/4-D-MINI-A

Part number: 162667

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	0.01 μm
Filter efficiency	99.9999 %
Condensate drain	Fully automatic
Structural design	Fiber filter
Max. condensate volume	22 ml
Bowl guard	Metal bowl guard
Symbol	00991551
Operating pressure	1.5 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:7:2] Inert gases
Temperature of medium	1.5 $^\circ\text{C}$... 60 $^\circ\text{C}$
Residual oil content	0.01 mg/m^3
Ambient temperature	-10 $^\circ\text{C}$... 60 $^\circ\text{C}$
Product weight	500 g
Type of mounting	With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS compliant
Compressed air filter material	Borosilicate glass fiber
Housing material	Die-cast zinc
Material of bowl	PC