

Service unit FRC-1-D-7-MAXI-A

Part number: 162769

FESTO



Data sheet

 General operating condition

Feature	Value
Size	Maxi
Series	D
Actuator lock	Rotary knob with detent
Mounting position	Vertical $\pm 5^\circ$
Condensate drain	Fully automatic
Structural design	Proportional standard oil mist lubricator
Max. condensate volume	80 ml
Grade of filtration	40 μm
Bowl guard	Metal bowl guard
Symbol	00991599
Pressure gauge	with pressure gauge
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Pressure regulation range	0.5 bar ... 7 bar
Max. pressure hysteresis	0.04 MPa
Max. pressure hysteresis	0.4 bar
Max. pressure hysteresis	5.8 psi
Normal nominal flow rate (normalized to DIN 1343)	8700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 $^\circ\text{C}$... 60 $^\circ\text{C}$
Ambient temperature	-10 $^\circ\text{C}$... 60 $^\circ\text{C}$
Product weight	2520 g
Type of mounting	With accessories
Pneumatic connection 1	G1
Pneumatic connection 2	G1
Housing material	Die-cast zinc
Material of bowl	PC