

# Flanged precision pressure gauge FMAP-63-4-1/4-EN

Part number: 162843

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Display range	0 bar ... 4 bar
Display range	1 psi ... 58 psi
Symbol	00991463
Conforms to standard	EN 837-1
Pressure gauge nominal size	63
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Structural design	Bourdon tube pressure gauge
Type of mounting	Front panel mounting
Operating medium	Inert gases Neutral liquids
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 MPa ... 0.4 MPa
Operating pressure	0 bar ... 4 bar
Operating pressure	0 psi ... 58 psi
Intermittent load factor	0.66
Measurement accuracy class	1
Degree of protection	IP43
Temperature of medium	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS compliant
Connection position	Centered on rear side
Pneumatic connection	G1/4
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	ABS
Inspection window material	SAN
Fastening ring material	Steel

<b>Feature</b>	<b>Value</b>
Housing colour	Black
Product weight	120 g
Scale	Double scale bar (außen) psi (inner scale)