

Pivot pin kit DAMT-V1-80-A

Part number: 163529

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	80
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Circuit boards, lines, electrical push-in connectors and coils are excluded
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	6 kN
Product weight	1494 g
Note on materials	RoHS-compliant
Material of screws	Steel Galvanized
Trunnion flange material	Steel, galvanized
Clamping piece material	Steel, galvanized
Rod material	High-alloy stainless steel