

Manifold block CPE14-PRSG-2

Part number: 164965

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Max. no. of valve positions	2
Burst pressure	3 MPa
Burst pressure	16 bar
Burst pressure	232 psi
Operating pressure	-0.09 MPa ... 1 MPa
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	950 g
Sub-base mounting type	With through-hole With H-rail
Pneumatic connection 1	G3/8
Note on materials	RoHS-compliant
Housing material	PA-reinforced