

# Manifold block CPE14-PRSE-2

Part number: 164967

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Max. no. of valve positions              | 2  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Product weight                           | 85 g   |
| Sub-base mounting type                   | With through-hole<br>With DIN rail                                 |
| Pneumatic connection 1                   | G3/8   |
| Note on materials                        | RoHS compliant   |
| Housing material                         | PA-reinforced  |