

Sub-base PAML-CP-90-HP3-G12

Part number: 1651541

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	90
Nominal width DN	36
Series	L
Operating pressure	0 MPa ... 5 MPa
Operating pressure	0 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C ... 60 °C
For use in the food industry	See supplementary material information
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	770 g
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy
Seals material	NBR
Material of screws	Stainless steel