

# Fiber-optic cable SOEZ-LLG-RT-0,5-M6X0,75

Part number: 165356

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value  |
|--|--|
| Method of measurement                        | Fiber-optic cable<br>Reflection light sensor |
| Ambient temperature                          | -20 °C ... 160 °C                            |
| Size   | M6x0.75                                      |
| Product weight                               | 34 g   |
| Housing material                             | Chrome-plated                                |
| Setting range, upper limit                   | 100 mm                                       |
| Ambient temperature of flexible installation | -20 °C ... 120 °C                            |
| Degree of protection                         | IP54   |
| LABS (PWIS) conformity                       | VDMA24364-B2-L                               |