

Fiber-optic cable SOEZ-LLG-RT-0,5-M6X0,75

Part number: 165356

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Method of measurement	Fiber-optic cable Reflection light sensor
Ambient temperature	-20 °C ... 160 °C
Size	M6x0.75
Product weight	34 g
Housing material	Chrome-plated
Setting range, upper limit	100 mm
Ambient temperature of flexible installation	-20 °C ... 120 °C
Degree of protection	IP54
LABS (PWIS) conformity	VDMA24364-B2-L