


Branching module FRM-H-D-MAXI

Part number: 170689

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Structural design	Branching module
Symbol	00991511
Operating pressure	0.025 MPa ... 1.6 MPa
Operating pressure	0.25 bar ... 16 bar
Standard nominal flow rate in main flow direction 1 -> 2	13500 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Inert gases
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:-:-] Inert gases
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	446 g
Pneumatic connection 3	G3/4
Pneumatic connection 4	G1/4
Note on materials	RoHS compliant
Housing material	Die-cast zinc