

# Plug socket MSSD-C-4P

Part number: 171157

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Type of mounting	On air solenoid valve with M3 central screw
Mounting position	Any
Product weight	22 g
Electrical connection	3-pin Angled socket Type A As per DIN EN 175301-803 Rectangular design MSC Rectangular design MSN1
Cable fitting	Pg9
Cable diameter	6 mm ... 8 mm
Nominal conductor cross section	≤1.5 mm <sup>2</sup>
Degree of protection	IP65
Ambient temperature	-25 °C ... 90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Housing material	Polymer
Housing colour	Black