

Blanking plug QSP10-PTB

Part number: 172976

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Size	Standard
Mounting position	Any
Design	Straight design
Pack size	1
Operating pressure for entire temperature range	0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	0.95 bar ... 10 bar
Operating pressure for entire temperature range	13.775 psi ... 145 psi
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	1.1 g
Type of mounting	Mounting pin
Pneumatic connection 1	Cartridge 10 mm
Note on materials	RoHS-compliant
Housing material	PA
Material of tubing seal	NBR