

Filter LF-1-D-5M-MAXI-A-NPT

Part number: 173707

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Maxi |
| Series | D |
| Mounting position | Vertical |
| Grade of filtration | 5 µm |
| Condensate drain | Fully automatic |
| Bowl guard | Metal bowl guard |
| Symbol | 00991520 |
| Operating pressure | 2 bar ... 12 bar |
| Normal nominal flow rate (normalized to DIN 1343) | 3800 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas |
| Temperature of medium | 5 °C ... 60 °C |
| Ambient temperature | 5 °C ... 60 °C |
| Type of mounting | With mounting bracket |
| Pneumatic connection 1 | 1 NPT |
| Pneumatic connection 2 | 1 NPT |
| Note on materials | RoHS-compliant |
| Compressed air filter material | PE |
| Housing material | Die-cast zinc |
| Material of bowl | PC |