

Fine filter combination LFMBA-3/8-D-MIDI-NPT

Part number: 173746

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Midi
Series	D
Mounting position	Vertical
Grade of filtration	0.01 µm
Filter efficiency	99.9999 %
Condensate drain	Manual, non-detenting
Bowl guard	Metal bowl guard
Symbol	00991740
Operating pressure	1 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [1:7:2] Inert gases
Temperature of medium	1.5 °C ... 60 °C
Residual oil content	0.01 mg/m ³
Ambient temperature	-10 °C ... 60 °C
Type of mounting	With accessories
Pneumatic connection 1	3/8 NPT
Pneumatic connection 2	3/8 NPT
Note on materials	RoHS compliant
Compressed air filter material	Borosilicate glass fiber
Housing material	Die-cast zinc
Material of bowl	PC