

Filter regulator LFR-3/4-D-7-MAXI-A-NPT

Part number: 173811

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical
Grade of filtration	40 µm
Condensate drain	Fully automatic
Max. condensate volume	80 ml
Bowl guard	Metal bowl guard
Symbol	00991587
Operating pressure	0.2 MPa ... 1.2 MPa
Operating pressure	2 bar ... 12 bar
Max. pressure hysteresis	0.4 bar
Normal nominal flow rate (normalized to DIN 1343)	10000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:8:4] Inert gases
Temperature of medium	5 °C ... 60 °C
Ambient temperature	5 °C ... 60 °C
Product weight	1370 g
Type of mounting	With retaining bracket
Pneumatic connection 1	3/4 NPT
Pneumatic connection 2	3/4 NPT
Note on materials	RoHS compliant
Housing material	Die-cast zinc
Material of bowl	PC