

Service unit FRC-3/4-D-5M-MAXI-A-NPT

Part number: 173881

FESTO



Data sheet

 General operating condition

| Feature | Value |
|---|--|
| Size | Maxi |
| Mounting position | Vertical |
| Condensate drain | Fully automatic |
| Grade of filtration | 5 µm |
| Symbol | 00991599 |
| Operating pressure | 0.2 MPa ... 1.2 MPa |
| Operating pressure | 2 bar ... 12 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.04 MPa |
| Max. pressure hysteresis | 0.4 bar |
| Max. pressure hysteresis | 5.8 psi |
| Normal nominal flow rate (normalized to DIN 1343) | 7000 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gases |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [6:8:-] Inert gases |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 2390 g |
| Type of mounting | With retaining bracket |
| Pneumatic connection 1 | 3/4 NPT |
| Pneumatic connection 2 | 3/4 NPT |
| Note on materials | RoHS compliant |
| Housing material | Die-cast zinc |
| Material of bowl | PC |