

Branching module FRM-1-D-MAXI-NPT

Part number: 173931

FESTO



 General operating condition

Data sheet

| Feature | Value |
|--|--|
| Mounting position | Any |
| Structural design | Branching module |
| Symbol | 00991510 |
| Operating pressure | 0 MPa ... 1.6 MPa |
| Operating pressure | 0 bar ... 16 bar |
| Standard nominal flow rate in main flow direction 1 -> 2 | 17400 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:-:-] Inert gas |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 772 g |
| Pneumatic connection 1 | 1 NPT |
| Pneumatic connection 2 | 1 NPT |
| Pneumatic connection 3 | G3/4 |
| Pneumatic connection 4 | G1/4 |
| Note on materials | RoHS-compliant |
| Housing material | Die-cast zinc |