


# Clevis flange SNC-32

Part number: 174383

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value   |
|----------------------------------|---|
| Size                             | 32  |
| Based on norm                    | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress  |
| LABS (PWIS) conformity           | VDMA24364-B2-L  |
| Ambient temperature              | -40 °C ... 150 °C   |
| Max. load capacity               | 0.9 kN  |
| Product weight                   | 93 g  |
| Note on materials                | RoHS-compliant  |
| Mounting material                | Die-cast aluminum   |
| Bolt material                    | Steel<br>Galvanized   |
| Material of screws               | Steel<br>Galvanized   |
| Fuse material                    | Spring steel<br>Galvanized  |