

# Pivot pin ZNCF-40

Part number: 174412

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                         |
|----------------------------------|-------------------------------|
| Size                             | 40                            |
| Based on norm                    | ISO 15552                     |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity           | VDMA24364-B2-L                |
| Ambient temperature              | -40 °C ... 150 °C             |
| Max. load capacity               | 1.5 kN                        |
| Product weight                   | 285 g                         |
| Note on materials                | RoHS compliant                |
| Mounting material                | Cast stainless steel          |
| Material of screws               | Steel<br>Galvanized           |