

# Pivot pin ZNCF-80

Part number: 174415

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	80
Based on norm	ISO 15552
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	6 kN
Product weight	1296 g
Note on materials	RoHS-compliant
Mounting material	Cast stainless steel
Material of screws	Steel Galvanized