

# Plug socket with cable KMEB-2-24-5-LED

Part number: 174845

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Switching position indication	LED
Type of mounting	On air solenoid valve with M2.5 central screw
Mounting position	Any
Product weight	400 g
Electrical connection	4-pin Socket, angled Form C as per DIN EN 175301-803
Nominal operating voltage DC	24 V
Protective earth connection	Available
Cable length	5 m
Cable diameter	6.2 mm
Cable design	3 x 0.75 mm <sup>2</sup>
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material of cable sheath	TPE-U(PUR)
Housing material	PA POM
Material of pin contacts	Bronze