

Plug socket with cable KMEB-2-230-2,5

Part number: 174846

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	On air solenoid valve with M2.5 central screw
Mounting position	Any
Product weight	200 g
Electrical connection	4-pin Socket, angled Form C as per DIN EN 175301-803
Nominal operating voltage AC	230 V
Protective earth connection	Available
Cable length	2.5 m
Cable diameter	6.2 mm
Cable design	3 x 0.75 mm ²
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU low voltage directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material of cable sheath	TPE-U(PUR)
Housing material	PA POM
Material of pin contacts	Bronze