

Mounting kit SMBR-8-50

Part number: 175099

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	50
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-20 °C ... 70 °C
Profile material	Wrought aluminum alloy
Note on materials	RoHS compliant
Retainer bracket material	POM