

Coupling EAMC-65-90-XX-25

Part number: 176038

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 2	25 mm
Size	65
Nominal length	90 mm
Mounting position	Any
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	417 kgmm ²
Product weight	535 g
Note on materials	RoHS-compliant