

Valve kit CPV14-BS-5/3G-1/8

Part number: 176057

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Valve function	5/3-way, closed
Pneumatic working port	G1/8
Operating pressure	2.5 bar ... 10 bar
Nominal width	6 mm
Mounting position	Any
Burst pressure	30 bar
Switching time off	30 ms
On switching time	22 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Shock resistance	30 g/11 ms as per EN 60068-2-27
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	190 g
Type of mounting	With through-hole
Pneumatic connection 2	G1/8
Note on materials	RoHS compliant
Seals material	NBR
Housing material	Die-cast zinc