

Valve kit CPV14-BS-5/3G-1/8

Part number: 176057

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Valve function | 5/3, closed |
| Pneumatic working port | G1/8 |
| Operating pressure | 2.5 bar ... 10 bar |
| Nominal width | 6 mm |
| Mounting position | Any |
| Burst pressure | 30 bar |
| Switching time off | 30 ms |
| On switching time | 22 ms |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Shock resistance | 30 g/11 ms according to EN 60068-2-27 |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 190 g |
| Type of mounting | With through-hole |
| Pneumatic connection 2 | G1/8 |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Housing material | Die-cast zinc |