

Foot mounting CRHNC-32

Part number: 176937

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	32
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	0.9 kN
Product weight	139 g
Note on materials	RoHS-compliant
Mounting material	High-alloy stainless steel
Material of screws	High-alloy stainless steel