

Clevis flange SNCB-50-R3

Part number: 176946

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Size | 50 |
| Based on norm | ISO 15552 |
| Variants | High corrosion protection |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Ambient temperature | -40 °C ... 90 °C |
| Max. load capacity | 2.5 kN |
| Product weight | 228 g |
| Note on materials | RoHS-compliant |
| Mounting material | Die-cast aluminum With protective coating |
| Bolt material | High-alloy stainless steel |
| Material of bearing | Polymer |
| Disc material | Steel, galvanized |
| Material of screws | High-alloy stainless steel |
| Fuse material | Spring steel, galvanized |