

Multi-pin plug distributor MPV-E/A12-M8

Part number: 177670

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	Alternatively: With through-hole With DIN rail
Product weight	120 g
Electrical connection technology I/O	M8 3-pin
DC operating voltage range	10 V ... 30 V
Acceptable current load per slot	1 A
Current rating	4 A
Degree of protection	IP65 In mounted state As per IEC 60529
Ambient temperature	-20 °C ... 80 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	Reinforced PA6
Socket material	Brass