

# Plug socket with cable KMEB-2-24-M12-0,5-LED

Part number: 177677

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Switching position indication	LED
Type of mounting	On air solenoid valve with M2.5 central screw
Mounting position	Any
Electrical connection	5-pin Angled socket Type C As per DIN EN 175301-803
Nominal operating voltage DC	24 V
Protective earth connection	Available
Cable length	0.5 m
Cable diameter	4.6 mm
Cable design	3 x 0.5 mm <sup>2</sup>
Degree of protection	IP65 As per IEC 60529
Ambient temperature	-5 °C ... 50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Material of cable sheath	TPE-U(PU)
Color cable sheath	Black
Housing material	PA POM
Housing colour	Transparent
Material of pin contacts	Bronze