

# Plastic pipe PQ-PA-22X2X3000

Part number: 177731

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Outside diameter	22 mm
Inside diameter	18 mm
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-25 °C ... 75 °C
Ambient temperature	-25 °C ... 75 °C
Product weight by length	0.13 kg/m
Color	Black
Material of pneumatic tubing	PA