

# Clamping component DADL-EC-Q11-50

Part number: 1796626

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                                |
|----------------------------------|--------------------------------------|
| Size                             | 50                                   |
| Design                           | for T-slot                           |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress        |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                    |
| Ambient temperature              | -10 °C ... 60 °C                     |
| Product weight                   | 140 g                                |
| Type of mounting                 | Screwed tightly<br>Clamped in T slot |
| Note on materials                | RoHS-compliant                       |
| Material of screws               | Steel<br>Galvanized                  |