


# Front panel valve SV/O-3-PK-3X2

Part number: 184135

FESTO



[PDF](#) General operating condition

## Data sheet

Feature	Value
Valve function	2x3/2 closed, monostable
Normal nominal flow rate (normalized to DIN 1343)	70 l/min
Pneumatic working port	PK-3
Operating pressure	0 bar ... 8 bar
Reset method	Mechanical spring
Nominal width	2.5 mm
Sealing principle	Soft
Mounting position	Any
Type of control	directly
Flow direction	Non-reversible
Symbol	00997337
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	34 g
Type of mounting	With through-hole
Pneumatic connection 1	PK-3
Pneumatic connection 2	PK-3
Seals material	NBR