

# Manual override HAB-1/4

Part number: 184586

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	7 mm
Mounting position	Any
Valve function	Exhaust element
Operating pressure	0 bar ... 10 bar
Standard nominal flow rate exhaust air 6→5 bar	165 l/min
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-20 °C ... 80 °C
Ambient temperature	-20 °C ... 80 °C
Max. tightening torque	15 Nm
Type of mounting	Screw-in
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS compliant
Housing material	Wrought aluminum alloy, anodized