

# Plug socket MSSD-ZBZC

Part number: 185521

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Maritime classification	See certificate
Type of mounting	On air solenoid valve with self-tapping screw
Mounting position	Any
Product weight	11 g
Electrical connection	Socket
DC operating voltage range	3 V ... 36 V
Nominal operating voltage DC	24 V
Current rating	1 A
Nominal conductor cross section	0.22 mm <sup>2</sup> ... 0.34 mm <sup>2</sup>
Degree of protection	IP50
Ambient temperature	-10 °C ... 50 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Contamination level	2
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing material	PA