

Filter LF-1/2-D-5M-MAXI-A

Part number: 186466

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Maxi
Series	D
Mounting position	Vertical $\pm 5^\circ$
Grade of filtration	5 μm
Condensate drain	Fully automatic
Structural design	Sinter filter with centrifugal separator
Bowl guard	Metal bowl guard
Symbol	00991520
Operating pressure	2 bar ... 12 bar
Normal nominal flow rate (normalized to DIN 1343)	3700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 $^\circ\text{C}$... 60 $^\circ\text{C}$
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gases
Temperature of medium	5 $^\circ\text{C}$... 60 $^\circ\text{C}$
Ambient temperature	5 $^\circ\text{C}$... 60 $^\circ\text{C}$
Product weight	1340 g
Type of mounting	With accessories
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Note on materials	RoHS compliant
Compressed air filter material	Protective grounding
Housing material	Die-cast zinc
Material of bowl	PC