

Branching module FRM-1/2-D-MAXI

Part number: 186524

FESTO



 General operating condition

Data sheet

Feature	Value
Mounting position	Any
Structural design	Branching module
Symbol	00991510
Operating pressure	0 MPa ... 1.6 MPa
Operating pressure	0 bar ... 16 bar
Standard nominal flow rate in main flow direction 1 -> 2	11700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Inert gases
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C ... 60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:-:-] Inert gases
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	706 g
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Pneumatic connection 3	G3/4
Pneumatic connection 4	G1/4
Note on materials	RoHS compliant
Housing material	Die-cast zinc