

Manifold block CPE14-PRSG-3

Part number: 187824

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Max. no. of valve positions | 3 |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Product weight | 130 g |
| Sub-base mounting type | With through-hole With DIN rail |
| Pneumatic connection 1 | G3/8 |
| Note on materials | RoHS compliant |
| Housing material | PA-reinforced |