

Cable socket ASI-SD-PG-M12

Part number: 18789

FESTO



 General operating condition

Data sheet

Feature	Value
Type of mounting	With union nut
Mounting position	Any
Product weight	27.6 g
Electrical connection	4-pin Socket, straight Screw terminal
Operating voltage range AC	≤125 V
Current rating	3 A
Cable fitting	Pg9
Connection cross section	0.75 mm ²
Degree of protection	IP65 IP67
Ambient temperature	-40 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Housing material	PA
Housing colour	Black
Material of union nut	Nickel-plated
Material of pin contacts	Bronze