

Cable distributor ASI-KVT-FK-S

Part number: 18797

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Type of mounting	With through-hole
Mounting position	Any
Product weight	7.2 g
DC operating voltage range	≤75 V
Operating voltage range AC	≤60 V
Current rating	3 A
Connection cross section	1.5 mm ²
Degree of protection	IP65
Ambient temperature with flexible cable installation	-5 °C ... 50 °C
Storage temperature	-30 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA
Material of pin contacts	Bronze