

# Suction gripper ESG-2

Part number: 189167

FESTO



 [General operating condition](#)

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Suction cup diameter	2 mm
Mounting position	Vertical
Special features	Anti-static
Structural design	Vacuum connection at top Vacuum connection at side with height compensation
Classification of suction cup holder	Size 1
Suction cup shape	Round, flat
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-30 °C ... 200 °C
Vacuum connection	M3 M10x1 QS-4 PK-3
Note on materials	RoHS-compliant
Suction cup material	BR FPM NBR PUR VMQ (silicone)