

# Vacuum suction cup holder ESH-HA-6-G

Part number: 189202

FESTO



 [General operating condition](#)

## Data sheet

| Feature                              | Value   |
|--------------------------------------|---|
| Nominal width                        | 10 mm   |
| Volume                               | 7.234 cm <sup>3</sup>                           |
| Mounting position                    | Any   |
| Structural design                    | Vacuum connection at top                        |
| Classification of suction cup holder | Size 6  |
| Operating medium                     | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class (CRC)     | 1 - Low corrosion stress                        |
| LABS (PWIS) conformity               | VDMA24364-A1-L                                  |
| Ambient temperature                  | -10 °C ... 60 °C                                |
| Product weight                       | 200 g   |
| Type of mounting                     | With locknut                                    |
| Suction cup mounting                 | M20x2   |
| Vacuum connection                    | G1/4  |
| Note on materials                    | RoHS compliant                                  |
| Retainer bracket material            | Quenched and tempered steel<br>High-alloy steel |