

# Vacuum suction cup holder ESH-HA-6-G

Part number: 189202

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	10 mm
Volume	7.234 cm <sup>3</sup>
Mounting position	Any
Structural design	Vacuum connection at top
Classification of suction cup holder	Size 6
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	200 g
Type of mounting	With lock nut
Suction cup mounting	M20x2
Vacuum connection	G1/4
Note on materials	RoHS-compliant
Retainer bracket material	Tempered steel High-alloy steel