

Vacuum suction cup holder ESH-HB-4-QS

Part number: 189209

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	5 mm
Volume	0.646 cm ³
Mounting position	Any
Structural design	Vacuum connection at side
Classification of suction cup holder	Size 4
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	27 g
Type of mounting	With internal thread
Suction cup mounting	M6
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retainer bracket material	Tempered steel High-alloy steel