

Vacuum suction cup holder ESH-HCL-1-QS

Part number: 189223

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Suction cup holder height compensator	10 mm
Nominal width	2.8 mm
Volume	0.489 cm ³
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C ... 60 °C
Product weight	20 g
Type of mounting	With lock nut
Suction cup mounting	Diameter 3 mm
Vacuum connection	QS-4
Note on materials	RoHS-compliant
Seals material	NBR Steel
Retainer bracket material	Tempered steel High-alloy steel