

Vacuum suction cup holder ESH-HCL-4-QS

Part number: 189229

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---------------------------------------|--|
| Suction cup holder height compensator | 20 mm |
| Nominal width | 3.4 mm |
| Volume | 1.78 cm ³ |
| Mounting position | Vertical |
| Structural design | Vacuum connection at top with height compensation |
| Classification of suction cup holder | Size 4 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | 0 °C ... 60 °C |
| Product weight | 47 g |
| Type of mounting | With lock nut |
| Suction cup mounting | M6 |
| Vacuum connection | QS-6 |
| Note on materials | RoHS-compliant |
| Seals material | NBR Steel |
| Retainer bracket material | Tempered steel High-alloy steel |