

# Vacuum suction cup holder ESH-HDL-3-PK

Part number: 189248

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Suction cup holder height compensator	20 mm
Nominal width	3 mm
Volume	0.252 cm <sup>3</sup>
Mounting position	Vertical
Structural design	Vacuum connection at side with height compensation
Classification of suction cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C ... 60 °C
Product weight	63 g
Type of mounting	With locknut
Suction cup mounting	M4
Vacuum connection	PK-4
Note on materials	RoHS compliant
Seals material	NBR Steel
Retainer bracket material	Quenched and tempered steel High-alloy steel